# **MB2** (MINI-Batcher)

# Features

- 5 Digit Scaling Factor
- Display Rate, Batch Size and (Number of Batches or Grand Total)
- Second B Relay Programmable for Output at Prewarn or selected Batch/Grand Total
- Pulse Input 10 kHz Max.
- Security Lockout on Flow Sensor Malfunction
- RS422/RS232 Serial Communication Option
- Modbus RTU RS422/RS485/RS232
- NEMA4X / IP65 Front Panel
- 30mV Magnetic Pickup Input Option
- 4-20mA or 0-20mA Analog Output Option

# put Option

# Application:

This miniature batcher is ideal for all batching applications. The display will show Batch Amount, Rate and Batch/Grand Total at the push of a button. The Start and Stop buttons make batching simple.

# **Description:**

The MINI-Batcher is a 6 digit totalizer and 4.5 digit ratemeter with two relay outputs. One output is dedicated to the batch amount (Preset A), the other can be activated for Prewarn or Batch/Grand Total. The unit can count up to the preset (reset to 0) or down from the preset (set to preset). Start, Stop and Reset functions can be activated from the front panel or remote inputs.

An analog output (assignable for Rate or Batch Amount) is available for data logging.

Several units can communicate to a host computer on a single RS232 or RS422 loop.

#### MINI-BATCHER MINI-

Low Cost, Pulse Input

**Batch Controller** 

# Water Batching Application



The MINI-Batcher is the central controller for this simple water batching application. The batcher accepts pulse inputs from a turbine flowmeter and uses relay(s) to control a solenoid valve.

A turbine flowmeter in the water line produces 100 pulses per gallon. The scaling factor (K-factor) in the MB2 is set to 10.0 to read gallons and 10ths on the display. The total decimal is set in the 10ths position. Relay A is used to control the valve. Preset A is used to set the batch size. We will use 25.0 gallons in this example. To start the batch of 25.0 gallons The START button is pressed and Relay A closes and energizes the solenoid valve. The turbine meter sends pulse signals to the A Input on MB2 and the unit begins to count gallons. The flow of water will continue until the count reaches 25.0, at which point the Relay A will open and the solenoid valve will close ending the batch of 25.0 gallons.

The batch can be halted at any time during the batch cycle by pressing the STOP button. At this point you can press START to proceed with the batch cycle or press RESET to start a new batch.



## Specifications:

Display: 6 digit, 0.55" High LED

#### Input Power:

110 VAC ± 15% or 12 to 15 VDC 220 VAC ± 15% or 12 to 15 VDC

24 VAC ± 15% or 12 to 15 VDC

Current: 250 mA DC max. or 6.5 VA (6.5W) AC

Output Power: (AC powered units only)

+12 VDC @ 50 mA, unregulated -10 + 50%

### **Temperature:**

Operating:

+32°F (0°C) to +130°F (+54°C)

Storage:

-40°F (-40°C) to +200°F (93°C)

Humidity: 0-90% Noncondensing

Memory: EEPROM stores data for 10 years if power is lost. Listing: CSA (File No. LR91109), CE Compliant,

NRTL/C pending

# Inputs:

- High Impedance DC pulse input 4-30 VDC (high), Open or 3:
  - 0-1 VDC (low), 10 kΩ impedance, 10 kHz max. speed.
- 3M: Mag. Input, accepts 30mV input (50 V max.) signals 10 KΩ imp. 5 kHz max.

# Stop / Reset:

Front Panel:

STOP/RST button stops batch if batch is running. Resets displayed value and control output if batch is stopped.

Remote:

- 4-30 VDC, positive edge: stops batch if batch is running, Resets batch amount if batch is stopped.
- NOTE: Hold either front or remote reset active to inhibit any start inputs.

Scaling Factor (K-Factor): A user programmable K-Factor is used to convert the input pulses to engineering units. The 5 digit K-Factor divider, with decimal keyed into any position, allows easy direct entry of any K-Factor from 0.0001 to 99999.

Presets: Two control outputs are provided. A 5 digit value can be entered for both presets. The decimal point location is the same as the counter (No decimal in Batch Total counter).

# PRESET A:

The preset A output is dedicated to the batch amount. When START is activated, Relay A will energize and remain on until the batch is complete or the batch is stopped.

### PRESET B:

The preset B output can be programmed to activate as a Prewarn (for two stage batch control) or activate on Batch Total (number of batches) or Grand Total (selectable).

When set for PREWARN, Relay B will energize when START is activated and drop out at Prewarn number before preset.

When set for Batch Total (number of batches) or Grand Total, Relay B will activate when the batch total or grand total counts up to preset B amount. The output ON time can be set for a duration (0.01 to 99.99 sec.) or latched (0.00 setting). If a value other than 0.00 is set for the duration, the batch total (number of batches) or grand total will auto-reset at preset B.

# **Control Outputs:**

#### Relays:

2 each N.O. Relay; 5 Amps 120/240 VAC or 28 VDC. (N.C. relay contacts and NPN transistor output available with solder jumpers.

# Analog Output:

An optional 4-20mA (0-20mA) output is available for the Mini-Batch series. The output can be programmed to track rate or batch amount. Connections are via a 2 terminal pluggable screw connector. Programming is accomplished by using the front panel in conjunction with rear dip switches. Accuracy: ±.25% FS worst case. Compliance Voltage: 3 to 30 VDC non inductive.

Lockout: Unauthorized front panel changes can be prevented by entering a user selected 5 digit code. The front panel can be completely locked out (except Start & Stop) or the preset can remain accessible.

Security: The Security feature is a missing pulse detection to prevent overrun in case of a flow sensor error or broken connection. The security can be set from 01 to 99 seconds. If a batch is started and the unit does not receive a signal from the sensor within the set amount of time the batch will stop and the display will show SECure to warn that an error has occurred. To clear the Security status enter the Lock code. To disable this feature enter 00 for the SEEr setting.

Ratemeter: Accuracy: 0.01% FS (±1 display digit).

The rate display updates once per second. The rate meter can be programmed to sample from 2 to 24 seconds maximum, and auto-range up to 5 digits of significant information. The ratemeter displays in units per second, minute or hour.

Batch or Grand Totalizer: In addition to viewing the batch amount, a second counter can be viewed. This counter is programmable to count either the number of batches (Batch Total) or the grand total count (Grand Total).

# RS232/RS422 with KEP Protocol:

If the serial interface option is supplied, up to 99 units can be linked together. (The terminal addressing the unit must be capable of driving all loads in the loop.) Unit status and new set points can be communicated by serial communication. Mode changes, however, must always be made on the front panel.

Data is received and transmitted over standard EIA RS232 or RS422 levels. Unit number, baud rate and parity are entered in the "Program Setting" set up mode and remain in memory even if power is off.

# RS232/RS422/RS485 with Modbus RTU Protocol:

The serial port can be used for data acquisition. The unit can address up to 247 units (The terminal addressing the unit must be capable of driving all loads in the loop.) The unit can communicate with a master device through a Modbus-RTU protocol. The data given for each parameter is in IEEE float format comprising of 2 words. The unit can be connected in a network.

Device ID: 01-247 Baud Rates: 300, 600, 1200, 2400, 4800, 9600 Parity: None, Odd, Even Protocol: Modbus RTU (Half Duplex)



Dimensions:





○ 12- A.C. INPUT

Ardering Information	
Example: MB2 A 3 1	
Series:	
MB2= MiniBatcher	
Operating Voltage:	
A= 110 VAC ± 15% or 12 to 15 VDC	E
<b>B</b> = 220 VAC ± 15% or 12 to 15 VDC	B∕ B∕
C= 24 VAC ± 15% or 12 to 15 VDC	AT I
Count Inputs:	CF
<b>3</b> = Standard, 4-30 VDC pulse inputs.	IB
3M = Mag. Input, 30mV input	me RS
Options	nts
1= RS232 Communications	•1
2= RS422 Communications	
3= Modbus RTU RS232	
4= Modbus RTU RS422/RS485	
A= Analog Output (4-20/0-20 mA)	
NOTE: RS232/RS422/RS485 & Analog Output options can not be	
combined	
Separate keyboard papel - order #34569	
NEMA4 wall mount enclosure available see LCN4X & MS821	

Explosion proof enclosure available, see XHV

Ethernet Port Server available, see IEPS RS-422/485 to RS-232 Communication Adaptor available, see CA285 Modbus DDE/OPC Server available, see KEPserver



Wiring: